



The Model T101 UV Fluorescence H₂S Analyzer



The Model T101 H₂S analyzer uses the proven UV fluorescence principle to measure hydrogen sulfide at levels commonly required for ambient air monitoring.

— With NumaView™ premium T Series software —

- Large, vivid, and durable color touchscreen display
- Lifetime technical support by phone and email
- All other T Series instrument platform features
- Standard two-year warranty



T101 Specifications

■ Ranges	H ₂ S SO ₂	Min: 0-50 ppb full scale Max: 0-10 ppm full scale Up to 0-20 ppm full scale (selectable, dual range supported)
■ Measurement Units		ppb, ppm, µg/m ³ , mg/m ³ (selectable)
■ Zero Noise		< 0.2 ppb (RMS)
■ Span Noise		< 0.5% of reading (RMS) above 50 ppb
■ Lower Detectable Limit		0.4 ppb
■ Zero Drift		< 0.5 ppb/24 hours
■ Span Drift		< 0.5% of full scale/24 hours
■ Lag Time		20 seconds
■ Rise/Fall Time		< 120 seconds to 95%
■ Linearity		1% of full scale
■ Precision		0.5% of reading above 50 ppb
■ Sample Flow Rate		650 cc/min ±10%
■ Power Requirements		100V-120V, 220V-240V, 50/60 Hz
■ Analog Output Ranges		10V, 5V, 1V, 0.1V (selectable)
■ Recorder Offset		±10%
■ Included I/O		1 x Ethernet: 10/100Base-T 2 x RS232 (300-115,200 baud) 2 x USB device ports 8 x opto-isolated digital outputs 6 x opto-isolated digital inputs 4 x analog outputs
■ Optional I/O		1 x USB com port 1 x RS485 8 x analog inputs (0-10V, 12-bit) 4 x digital alarm outputs Multidrop RS232 3 x 4 - 20mA current outputs
■ Operating Temperature Range		5 - 40°C
■ Dimensions (HxWxD)		7" x 17" x 23.5" (178 x 432 x 597 mm)
■ Weight		Analyzer: 41 lbs (18.3 kg)

Specifications subject to change without notice. ¹
All Specifications are based on constant conditions



TELEDYNE API
Everywhereyoulook™

9970 Carroll Canyon Road ■ San Diego, CA 92131
Ph. 858-657-9800 Fax 858-657-9816
Email api-sales@teledyne.com

For more information about the Teledyne API family of monitoring instrumentation products, call us or visit our website at:

www.teledyne-api.com

© 2019 Teledyne API
Printed documents are uncontrolled. SAL000042C
(DCN 8062) 01.10.19

